



9313-EW



VIDEO

Product Description

Three gang electrical box for use with nonmetallic sheathed cable

Brand: fiberglassBOX™
Catalog #: 9313-EW

Carton Quantity: 25
Carton Weight: 17 lb.

Height: 3-1/4 in.
Width: 5-15/16 in.
Depth: 2-7/8 in.
Volume: 42.5 cu. in.
Type of Installation: Old Work
Wall Box
Number of Gangs: 3

UPC: 085339100935
UNSPSC: 39121308
Country of Origin: United States of America

FEATURES

Machine tapped device holes, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures, Speed "K" Clamps bulk packed

APPLICATION

Old work residential construction 2 HR fire resistive walls

STANDARDS

ANSI / UL 514C: File No. E30594



FIRE CLASSIFICATION

Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)

COLOR

Beige/tan

ADDITIONAL MATERIALS

Galvanized steel brackets and plated carbon steel fasteners

MATERIAL

Fiberglass reinforced polyester BMC

Polyvinyl chloride clamps

MOUNTING

Metal wing brackets/metal ears wall compression