




**Conduit Fittings-PVC Coated**  
**T&B Catalog Number:**

**UPC Number:** XJG64-G  
**Status:** 70450841772  
**Description:** Active

PVC Coated XJG Rigid Conduit Expansion Coupling with Internal Bonding Jumper, 2 Inch/53 Metric, Body is Malleable Iron with Zinc Plating, Internal Bonding Jumper is Tinned Copper Braid, Packing PTFE/Synthetic Fiber Material, 4 Inch/101.60 Millimeters Movement, Diameter 3.86 Inch/98.04 Millimeters, Length 11.25 Inch/285.75 Millimeters, Height 4.18 Inch/106.17 Millimeters, Gray



**Features**

- No disassembly necessary to install
- True internal bonding jumper, no external grounding strap required
- Tamper-proof internal jumper protected from the environment
- Exceeds code requirements for long conduit runs to permit linear movement

**Application**

Allows for the contraction and expansion of a conduit run without reducing the mechanical or bonding integrity of the raceway.

**General**

Trade Size (inches)	2
Material	Malleable Iron
Finish	PVC Coated
Color	Dark Gray

**Dimension Information**

Pipe Size (Metric Size Designator*)	53
Diameter (inches)	3.86
Length (inches)	11.25
Height (inches)	4.18
Movement (inches)	4

**Technical Information**

Chemical Resistance Chart Available on Website

**Specifications**

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

## Packaging

Package in Units	3
T&B Sold in UOM	Each
T&B Weight Per UOM	9.9 lbs. Each

## Application Support

Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

## Notes

Metric size designator (ANSI C80.1 - 1994)  
Dimensions shown are for uncoated coupling.

## Certifications

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:  
E 23018

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com