



S8455

FB32T8/741 /U6 /ENV
32 watt; T8; U-Bend Fluorescent; 4100K Cool White; 75 CRI;
Medium Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8455

Item Number	Product Line	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code
S8455	HyGrade	045923084553	32	T8	Medium Bi Pin	G13	FB32T8/741 /U6 /ENV
MOD In Inches	Nominal Length	Leg Spacing	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color
1.00"	22.6"	6"	2750	2475	20000	4100	Cool White
Pack	CRI	Hg Content		RoHS Compliant			
16	75	9.0 mg		Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

