

MINKA-LAVERY®

Item #: 4365-281	UPC Code: 747396071954
Product Family Name: Harbour Point	Finish: HARBOUR POINT BRONZE
Category: Flush Mount	Category Type: Flush Mount
Certification E127416	
Patents	
Notes:	



Image File Name:
4365-281--
1377125441.jpg



MEASUREMENTS

Width: 13.5	Length: 13.5	Height: 6.5	Extension: 6.5
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 4.85
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 2	Light Type: A19 Med			
Max Bulb Wattage: 60	Socket: E26 Med			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Glass
Part No.: G4365	Quantity: 1
Width: 12.25	Height: 4.25
	Length: 12.25



SHIPPING

Carton Width: 15.000	Carton Height: 8.000	Carton Length: 15.000
Carton Weight: 7.260	Carton Cubit Feet: 1.042	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



Damp Location
Yes



Title 17
Yes



UL Listed
Yes