



4-11/16 IN. SQUARE EXPOSED WORK

4-11/16 in. Square Exposed Work Covers
30-60A Receptacle 2.625 in. Dia.

A29



Catalog #: 888

APPLICATIONS

RACO® surface covers are used to support switches or receptacles in areas where the box is surface mounted or positioned in exposed work applications
N/A

PRODUCT FEATURES

RACO® exposed work covers include required hardware for mounting the receptacle(s)
RACO® exposed work covers meet the requirements of the 2014 NEC Article 250.146(A). No bonding jumper is required for covers with: (1) Crushed corners (2) Two or more device attachment screws (3) A lockwasher or equivalent
Hardware and cover are packed in a poly-bag with printed catalog number, compliances and installation instructions

UL LISTED

File E195978

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_Steel_Boxes_and_Covers.pdf

GENERAL PRODUCT INFORMATION

Country of Origin: USA

PRODUCT MEASUREMENTS

Cubic Inches (cm3): 10.3 (168.8)
Wt. Ea. (Lbs.): 0.450
Product Length (in.): 0.50
Product Width (in.): 4.69
Product Height (in.): 4.69

PACKAGING

Minimum Pack Qty.: 10
Std. Pkg.: 10
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 45.00
Ship Carton Length (in.): 10.00
Ship Carton Width (in.): 4.31
Ship Carton Height (in.): 5.25
Ctn Weight (Lbs.): 4.94
Pallet Qty: 2880
UPC Number: 050169008881
I2of5: 50050169008886