

APPLIANCE AND FIXTURE WIRE

High-Temperature Lead Wire

SFF-2/SRML

150C -600 Volt -UL Listed



CONSTRUCTION

Conductor	- Flexible stranded tinned copper
Insulation	- Silicone rubber
Jacket	- Fiberglass braid with a high temperature finish

Applications:

- Suitable for UV, ozone, and moisture exposure
- Suitable for applications to -60C

Standards:

- UL Listed

Part #	AWG	Stranding	Insulation Thickness	Nom. O.D.	Lbs./M'
C61801-XX	18	16	.030"	.120"	12
C61601-XX	16	26	.030"	.130"	16
C61401-XX	14	41	.030"	.150"	22
C61201-XX	12	65	.030"	.170"	32
C61001-XX	10	105	.045"	.230"	54

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

Insert the color number in the -XX location:

- 01 = Black
- 02 = White
- 03 = Red
- 04 = Green
- 05 = Blue
- 06 = Gray
- 07 = Orange
- 08 = Yellow
- 09 = Purple
- 10 = Brown