



Representative

**Catalog Number:** 54918BE  
**Product ID:** 7TAH007900R0015  
**UPC Number:** 78621089821  
**EAN Number:** 05414363144496  
**Status:** Active

Copper One-Hole Lug, Long Barrel, Blind End, Max 35kV, Wire Size 500 kcmil, 1/2 Inch Bolt Size, Tin Plated, Die Code 87, Die Color Code Brown

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Long Barrel Copper Lug
Standard	UL E9809
Cable Size	500 kcmil
Stud Size	1/2 Inch
Number Of Holes	1
Material	Copper
Color	Brown

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

### Packaging

Inner Quantity	6
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	60
Outer Dimensions (inches)	24x11x4
Weight Uom	47 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta01025-tb2

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)