



GE
Lighting

68978 - 70PARHIR+3KF25P1

70PARHIR+3KF25P1

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Skirt
Base Type	Screw-In
Bulb Material	Sodalime glass
Filament	CC-8
Rated Life Hours-nominal	3000 h
Primary Application	Indoor and outdoor Floodlight
Product Technology	Halogen
Base	E26/50x39
Bulb Shape	PAR38

PHOTOMETRIC CHARACTERISTICS

Beam Spread	25 deg
Center Beam Candle Pwr Candela	4500 cd
Nominal Initial Lumen per Watt	19
Initial Lumens-nominal	1305 lm
Color Rendering Index-CRI	100

PRODUCT INFORMATION

Product Code	68978
Description	70PARHIR+3KF25P1
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168689786
Standard Package GTIN	00043168689786
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168689786
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168689786
Standard Package GTIN	10043168689783
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168689786

DIMENSIONS

Diameter	4.75 in
----------	---------

ELECTRICAL CHARACTERISTICS

Burn Position	Universal
Input Voltage [nom]	120 V
Rated power (Watts)	70 W