



WhisperWarm™ Lite - Quiet, Fan/Heater/Light Solution, 110 CFM

FV-11VHL2

MORE DETAILS

- Static Pressure (in inches w.g.) 0.1
0.25
- Air Volume (CFM) 110 @ 0.1" static pressure
89 @ 0.25" static pressure
- Noise (sones) 0.7 at 0.1" static pressure
- Power Consumption (Watts) 30.6 at 0.1" static pressure
30.5 at 0.25" static pressure
- Energy Efficiency (CFM's/Watt) 3.6 at 0.1" static pressure
2.9 at 0.25" static pressure
- Speed (RPM) 812 at 0.1" static pressure
956 at 0.25" static pressure
- Current (Amps) 0.25 at 0.1" static pressure
0.25 at 0.25" static pressure
- Combined Amps 12.5
- Power Rating (V/Hz) 120/60
- Motor Type Condenser
- Type of Motor Bearing Ball
- Thermal Fuse Protection Yes
- Blower Wheel Type Sirocco
- Duct Diameter (inches) 4"
- Mounting Opening (inches sq.) 17 3/8" x 12 5/8"
- Grille Size (inches sq.) 18 1/8" L x 13 5/16" W
- Light Yes

- o Lamp Watts 2 x 18 watts
- o Lamp Color Rendering Index 84
- o Lamp Color Temp. (Kelvin) 3500
- o Lamp Rated Average Life (hrs) 10,000
- o Lamp Model # FDS18E35/4
- o Night Light Yes
- o Night Light Lamp Watts 4
- o Heater Yes
- o Heater Stainless Steel Sheathed Element Yes
- o Heater Directional Louver No
- o Heating Element Watts 1400
- o Heater Blower Fan (CFM) 90
- o Heater Blower Fan (Watts) 25
- o UL Listed for Tub/ Shower Enclosure No
- o Washington State VIAQ Code Yes
- o California Title 24 Compliant Yes
- o Mfg in ISO 9001 Certified Facility Yes
- o Gross Weight (lbs.) 22.7

UPC037988870660
