



Select a Language



SEARCH

Supplier Center Distributor Center

BROWSE PRODUCTS

Category: -- Select -- | Browse by Brand: --Select--

PRODUCTS

- Bending
- Bolt Cutters
- Cable Termination
- CATV/Broadband Instruments
- Connectors
- Electric Test Instruments
- Fasteners
- Fiber Connections
- Fiber Optic Instruments
- Fishing
- Hydraulic Tools
- Knockout Sets
- Material Handling
- Network Instruments
- Pipe Tools
- Power Tool Accessories
- Professional Hand Tools
- Pulling
- Safety Products
- Storage
- Telco Instruments
- VDV Instruments
- VDV Termination
- VDV Tools
- Wire Termination

[Cable Termination](#) > [DIELESS CRIMPING TOOLS](#) > [Battery Dieless](#) > CRIMPING TOOL, DIELESS 12T-LI BAT 120V C

CRIMPING TOOL, DIELESS 12T-LI BAT 120V C

Images Video



SAVE PRODUCT TO PDF

Related Products



User Reviews
(No Reviews Yet.)

Cat No: **EK12IDL11** UPC No: **783310520481** [Request Product Info or Demo ▶](#) [Where to Buy ▶](#)

Description	Specifications	Documents	Reviews
- Accessory : 12274 UPC 12274 Carrying Strap - Battery : 18 V, 3.0 AMP-HR Lithium-Ion - Battery Charge Time : 1 HR - Crimping Capacity : 4 AWG - 1000 KCMIL Copper Color Coded Lugs And Splices, 6 AWG - 1000 KCMIL Aluminum Color Coded Lugs And Splices 1000 KCMIL - Crimping Force : 12.000 TON - Height : 14-1/2 IN (368.000 MM) - Overall Length : 16-1/2 IN (420.000 MM) - Replacement Part : 52178 UPC 52178 120V Charger, 52179 UPC 52179 12V Charger, 52180 UPC 52180 230V Charger, 52176 UPC 52176 18V 3.0 Ah Li-ion Battery, 10118 UPC 10118 EK12IDL Carrying Case - Rotation : 350° - Standard : C/US UL Listed - Sub Brand : Gator - Type : Battery Powered, Dieless - Weight : 15.000 LB (6.800 KG)			

