

Ocal®

Conduit-PVC Coated
T&B Catalog Number:

UPC Number:

Status:

Description:

COND3/4-G

70450826102

Active

PVC Coated Conduit, Pipe Size 3/4 Inch/21 Metric, Outside Diameter with PVC 1.13 Inch/28.70 Millimeters, Nominal Wall Thickness with PVC .139 Inch/3.53 Millimeters, Length without Couplings 9 Feet 11-1/4 Inch /3.03 Meters, Hot-dip Galvanized Steel, Gray

Features

A minimum .040 in. (40 mil) PVC coating on the exterior.

A nominal .002 in. (2 mil) blue urethane on the interior.

Color coded thread protectors on each end.

Blue urethane coating over Hot-Dip Galvanized threads.

General

Material	Steel
Finish	Hot-Dip Galvanized
Color	Dark Gray
Thread Protector Color	Red

Dimension Information

Pipe Size (Metric Size Designator*)	21
Size (inches)	3/4
O.D. Steel Only (inches)	1.050
O.D. Steel Only (mm)	26.7
O.D. with PVC (inches)	1.130
O.D. with PVC (mm)	28.7
Nominal Wall Thickness-Steel Only (inches)	0.107
Nominal Wall Thickness-Steel Only (mm)	2.71
Nominal Wall Thickness with PVC (inches)	.147
Nominal Wall Thickness with PVC (mm)	3.73
Nominal Inside Diameter (inches)	0.836
Nominal Inside Diameter (mm)	21.2
Cross Section Area (square inches)	0.533
Cross Section Area (mm)	13.53
Length without Couplings	9' 11-1/4"
Length without Couplings (mm)	3.03
Minimum Weight Per Foot (lbs)	1.05
Minimum Weight Per Foot (kil)	47.63

Technical Information

Chemical Resistance Chart Available on Website

Specifications

Available on Website



Ocal Specification Guide-1995 Master
Format-PDF

Ocal Specification Guide-1995 Master Format-DOC	Available on Website
--	----------------------

Ocal Specification Guide-2004 Master Format-PDF	Available on Website
--	----------------------

Ocal Specification Guide-2004 Master Format-DOC	Available on Website
--	----------------------

Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	900
T&B Sold in UOM	Feet
T&B Weight Per UOM	1.24 lbs. Each

Application Support

T&B Sales Drawings	wsd-000042
Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

Notes

Metric size designator (ANSI C80. 1-1994)

Coupling(s) shipped with conduit are packaged separately

Certifications

RoHS Compliance	No
-----------------	----

Certifications



File Nbr:
E 46453

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com