

Madison Collection
1 Light Outdoor Wall Light - Madison in Black
9655BK (Black (Painted))

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Dimensions

Height	17.00"
Width	9.25"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Alternate	INCA	60W	4071CLR	

Ordering Information

Product ID	9655BK
Finish	Black (Painted)
Available Finishes	BK, TZ
Collection	Madison Collection

Dimensions

Extension	10.25"
Height from center of Wall opening	6.50"
Base Backplate	4.50 X 7.75
Weight	5.00 LBS

Specifications

Material	Aluminum
Glass Description	Clear Beveled

Electrical

Voltage	120V
---------	------

Qualifications

Safety Rated	Wet
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	1
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19