



Liquidtight Flexible Non-Metallic Conduit & Fittings

T&B Catalog Number:

15105-100

UPC Number:

03448123355

Status:

Active

Description:

1/2 Inch Black Non-metallic Conduit, 100 Foot Coil

Features

Extra strong and flexible to withstand repetitive motions.

Non-conductive and non-corrosive.

Resistant to oil, acid, ozone, and alkaline.

Lightweight for easy handling, transportation and installation.

Crush, abrasion and strain resistant.

Provides superior wire protection.

Smooth interior ideal for pulling cable, no jagged edges.

Rated for continuous use at 60 degree C (140 degree F) ambient.

UL recognized to UL Standard 1696

Application

Repetitive flexing arms

Robotics

Machine tools

Automatic/moving machinery

Control and Motor

General

Material Non-Metallic

Color Black

Dimension Information

Size (inches) 1/2

Average O.D. (inches) 0.83

Average I.D. (inches) 0.627

Nominal Size (inches) 1/2

Coil Length (feet) 100

Packaging

T&B Order Multiple 100

Package in Units 100

T&B Sold in UOM Feet

T&B Weight Per UOM 10.69 lbs. per 100

Application Support

Product Overview-Carflex Liquidtight Flex-Available on Website
ible Tubing

Certifications

RoHS Compliance Yes

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com