



S2257

70PAR38/HAL /XEN /FL /120V
70 watt; Halogen; PAR38; Clear; 1500 Average rated Hours;
1380 Lumens; Medium Skirted base; 120 volts

Features

- Energy Saving Halogen
- Bright, Crisp light
- Indoor / Outdoor
- Uniform light output



S2257

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S2257	045923022579	70	120	PAR38	Medium Skirted	E26SK	70PAR38/HAL /XEN /FL /120V
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	5-5/16"	4-3/4"	CC-8	1380	3000	Warm White	1500
Pack	Package Type	Beam Spread Deg	CBCP	Dimmable/Non-Dimmable	RoHS Compliant		
15	Box	30	2800	Dimmable	Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

