



Powering Business Worldwide

pe.eaton.com



Quicklag Industrial Thermal-Magnetic Circuit Breaker

QBHW1015

UPC:786679392003

Dimensions:

- **Height:** 4.8 IN
- **Length:** 3.9 IN
- **Width:** 1.2 IN

Weight:.3 LB

Notes:Switching duty rated for 120V fluorescent light applications, HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag
- **Amperage Rating:** 15A
- **Interrupt Rating:** 22 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Circuit Breaker Type:** QBHW
- **Trip Type:** Non-Interchangeable
- **Mounting:** Bolt-on
- **Quantity:** 24

Supporting documents:

- [Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data
