






1128/1102P1
Standard Incandescent

6" Aperture White Diffuser Reflector Trim



1128/1100 DEEP IC Series
Incandescent Insulated Ceiling



1128/1103R
Lytefiring™ Non-IC
Remodeler Ring

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Reflector Trim	Frame-In Kit — See Individual Frame-In Kit Specification Sheets							
1128 White Diffuser	LED				Fluorescent			
	Frame-In Kit	Installation Type	Lamping	Height	Frame-In Kit	Installation Type	Lamping	Height
	1101LED 1100LEDREM L56LED	Non-IC	LED	6 5/8"	1104F13 Series	IC	(1) Triple 13W (GX24q-1)	7 1/2"
		Non-IC Remodeler	LED	6 5/8"	1104F18† Series	IC	(1) Triple 18W (GX24q-2)	7 1/2"
	Non-IC Retrofit	LED	6 5/8"					
	Incandescent				1100FTU Series	Non-IC	(1) Triple 26/32W (GX24q-3)	6 3/4"
	Frame-In Kit	Installation Type	Lamping	Height				
	1102P1 1103R	Non-IC Non-IC Remodeler	100W A19	6 5/8" 6 5/8"	1100AICMFT	AirSeal® IC	(1) Triple 26W (GX24q-3)	6 3/4"
	1102P1 1103R	Non-IC Non-IC Remodeler	100W A19	6 5/8" 6 5/8"	1910XFH1	Conversion Kit	(1) Quad 13W (GX23-2)	6 3/4"
	1100IC 1100AICM 1100DICM 1100DAICM	IC AirSeal® IC Deep IC Deep AirSeal® IC	60W A19	7 5/16" 7 5/16" 9 1/4" 9 1/4"	1910XDH1	Conversion Kit	(2) Quad 13W (GX23-2)	6 3/4"
	1104ICX/N	AirSeal® IC	52W A19	7 1/4"				
1104IC/N 1104ICR	Non-IC Non-IC Remodeler	60W A19	7 1/2" 7 1/2"					
					† Use Upper Slot for 18W Triple Tube Lamp. ‡ Use upper slot for 26W Triple Tube Lamp.			

Features

- Reflector:** Hydroformed aluminum, .040 minimum thickness; Anobrite® (anodic-processed) semi-specular finish for permanent reflectivity; matte white trim flange.
- White Diffuser:** Provides soft, widespread illumination with light bezel to reduce brightness transition to ceiling.
- Lens Bezel:** Spun aluminum, .040" thick. Matte white finish.
- Frame-In Kit:** (1102P1 standard frame shown). Other frames listed above and shown on the right. See Frame-In Kit specification sheets for more details.

Options & Accessories

Retaining Clips: 1955 - For installing in existing ceiling.

Labels

U.L. (Suitable for Wet Locations - Covered Ceiling Only), I.B.E.W.

Job Information

Type:

Job Name:


Cat. No.:

Lamp(s):

Notes:


631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710
We reserve the right to change details of design, materials and finish.
www.lightolier.com © 2009 Philips Group • E0209

Fresnel Lenslite




Use quick calculator chart to determine the spacing of 2 Lt. Watt Quad Tube units (1126) for a desired level of illumination. Conversion Factors: 1 Lt. 13W Quad Tube, F.C. x 0.7. 100W A19, F.C. x 1.4.

White Diffuser




Use quick calculator chart to determine the spacing of 2 Lt. 13Watt Quad Tube units (1128) for a desired level of illumination. Conversion Factors: 1 Lt. 13W Quad Tube, F.C. x 0.8. 100W A19, F.C. x 1.95.

SPACING RATIO = 1.6



SPACING RATIO = 1.2



To convert lighting data for a lower wattage incandescent lamp of the **same type**, multiply the footcandle (or candlepower) values by the ratio of the lumens of the two lamps. The coefficients of utilization remain the same.

Job Information

Type:

631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710
We reserve the right to change details of design, materials and finish.
www.lightolier.com © 2009 Philips Group • E0209