


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YGHA282NTN
 7818101007833
 TERMINAL-TIN PLATED
 Active

Web Use
 BURNDY Product Line

Thickness
 B Length (in)
 D - in
 Pad Width (in)
 E - in

Dimensional

0.30
 1.18
 3.00
 1.22
 1.75

General

Product Description

Heavy Duty Irreversible
 Compression Terminals, 4/0 str.,
 4.94 in L, Tin Plated, Heavy Duty
 Irreversible Compression
 Terminals

Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)

N/A
 4/0 AWG

Type of Plating
 Connector Type
 Plated (Yes or No)
 Index Number

Physical

Tin - Electro Plated
 Terminal
 Y
 17

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications

Y
 Y
 Y
 Compliant
 N
 N
 UL468A-468B,UL467,IEEE 837

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175