



Representative Image

Catalog No. THQP120

Description: ASM THQP C/B 1 POLE 120/240V

UPC No 783164085686

Products > Circuit Breakers > Residential Circuit Breakers > Feeder Plug-in Circuit Breakers

THQP breakers are a smaller, smarter solution for today's cost- and quality-conscious contractors and homeowners. Half the width of standard breakers, they allow use of smaller load centers and for maximum savings of space and money. GE is the only manufacturer that gives you this cost advantage without sacrificing flexibility. THQP breakers are one-half the width of standard GE breakers but identical in design. They are available from 15 to 50 amps and in single and two pole construction.

Descriptors

Category	Feeder Plug-in Circuit Breakers
GO Schedule	R5

Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120 Vac, 120/240 Vac
Poles	1
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Wire Range (Cu/Al)	14-8 kcmil / 12-8 kcmil
Product Line	Q-Line (Plug-In)
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR, SWD
GSA Compliance	Yes

Classifications

UL File #	E11592
-----------	--------

Publications

Title	Publication No.	Publication Type
Q-Line Plug-In MCCB, 100A Frame 1-, 2- Pole, Drawing 1-Page fully dimensioned outline drawing in .pdf format	139C5337-SH1	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.