



Liquidtight Flexible Metal Conduit Fittings
T&B Catalog Number:

UPC Number: 5232GR
Status: 78621089983
Description: Active

1/2 Inch External Bonding Liquidtight, Flexible Metal Conduit Connector, With Revolver Lug, With Tin Plated Cu Alloy Lug for AWG #14 to #2 Ground Wire, for Use In Wet Locations, 25 Pieces

Features

Ability to install quickly with low torque effort

Application

To positively bond conduit to box or enclosure

General

Trade Size (inches)	1/2
Material	Steel
Finish	Electro Zinc Plated/Chromate Coating
Ground Wire	14-8

Dimension Information

Dimension A (inches)	1 3/8
Dimension B (inches)	1 9/16
Dimension C (inches)	9/16
Conduit Size (inches)	1/2

Specifications

3dmodel Available on Website

Packaging

T&B Inner Pack	25
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	20.5 lbs. per 100

Certifications

RoHS Compliance No

Certifications



File Nbr:
E 3060

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com