

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3924-20

Melon

One-light flush mount with dome shaped alabaster glass, solid trim and decorative knobs. Center lock-up with matching finial.

Category: Close-to-Ceiling

Finish: Antique Bronze (painted)

Construction: Steel construction

Glass: Alabaster glass bowl



Diameter: 11-3/8"

Height: 5-1/2"

Glass: 8-7/16" dia.

Height: 3-1/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling flush mounted</p> <p>Mounting strap for outlet box included</p> <p>Ceiling pan covers a standard 4" hexagonal recessed outlet box</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p>	<p>Quantity: 1</p> <p>60W Medium Base</p> <p>Medium ceramic socket</p>	<p>UL-CUL Damp location listed</p> <p>1 year warranty</p> <p>Companion fixtures are available</p>