

**MASONRY BOXES & PARTITIONS****Masonry Boxes, 3-1/2 in. Deep - Nongangable with Conduit KO's  
1-Gang, 1-31/32 in. Wide****A58**

Catalog #: 695

**APPLICATIONS**

RACO® Masonry boxes are designed to accommodate the mounting of switches or other devices in masonry walls  
 2-1/2" deep boxes are used in 4" block walls, 3-1/2" deep boxes are used in 6" or 8" block walls

**PRODUCT FEATURES**

Rugged welded design does not fall apart during construction  
 Available from one to six gang configurations in both 2-1/2" and 3-1/2" depths  
 Rectangular shape fits square cuts in block  
 Large volume design allows for additional work room inside the box  
 Standard 1/2" and 3/4" concentric knockouts  
 Device ears inside the box prevent mortar from getting in the device holes  
 Steel voltage partition #971 fits all 2-1/2" or 3-1/2" depths  
 Standard wall plates can be used  
 N/A

**UL LISTED**

File E195978

**COMPLIANCES**

MSDS  
[www.hubbell-rtb.com/certifications/Hubbell-RACO\\_MSDS\\_for\\_Steel\\_Boxes\\_and\\_Covers.pdf](http://www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_Steel_Boxes_and_Covers.pdf)

**GENERAL PRODUCT INFORMATION**

Wiring System: Conduit

**CONFIGURATION**

End Knockouts: 4 Conc.  
 Drawn or Welded: Welded  
 Gangs: 1  
 Side Knockout(s): 10 Conc.  
 Bottom Knockouts(s): 2 Conc.

**DRAWING DIMENSIONS**

Dimension A: 3-1/2 in.  
 Dimension B: 1-31/32 in.

**PRODUCT MEASUREMENTS**

Depth: 3-1/2 in.  
 Cubic Inches (cm3): 22.5 (368.7)  
 Wt. Ea. (Lbs.): 0.836  
 Product Length (in.): 3.50  
 Product Width (in.): 3.75  
 Product Height (in.): 1.97

**PACKAGING**

Minimum Pack Qty.: 25  
 Std. Pkg.: 25  
 Product UPC-A Labeled: No  
 Weight (Lbs. Per/C): 83.60  
 Ship Carton Length (in.): 13.00  
 Ship Carton Width (in.): 6.50  
 Ship Carton Height (in.): 10.75  
 Ctn Weight (Lbs.): 20.90  
 Pallet Qty: 2275  
 UPC Number: 050169906958  
 I2of5: 50050169906953