



Representative Image

## Catalog No. TLM1212CCU

Description: 12 CIR. 125 A CONVERTIBLE L/C

UPC No 783164112313

Products > Load Centers > Residential Load Centers > Single Phase - USA

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, except where noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- No lock provision available. Use compatible load center with the suffix C24 with a TDL106 for locking provision
- For a listing of CSA Listed load centers, visit [www.geelectrical.com](http://www.geelectrical.com)

### Descriptors

Category	Single Phase - USA
GO Schedule	RD

### Specifications

Input/Output Voltage	120/240V ac
Type	Standard
Interrupting Capacity Rating	65
Amperage	125 A
Device Type	Convertible
Enclosure	Indoor Type 1 Enclosure, Combination
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	0
1" Space	12
1/2" Space	42, 4, 24, 16, 20, 32, 40
Feed	Either
Door	Yes
GSA Compliance	Yes

## Publications

Title	Publication No.	Publication Type
<a href="#">Indoor Load Center</a> 1 page outline drawing in pdf format.	10103091-SH64	Drawings-Outline and Dimensional
<a href="#">PowerMark Gold 100-125A, 12/24 Circuit Load Center</a> Rev. B.	DET-582	Application and Technical

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.