



Catalog No. TLM2020CCU

Description: 20 CIR. 200 A CONVERTIBLE L/C

UPC No 783164112375

Products > Load Centers > Residential Load Centers > Single Phase - USA

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit www.geelectrical.com

Descriptors

Category	Single Phase - USA
GO Schedule	RD

Specifications

Input/Output Voltage	120/240V ac
Type	Standard
Interrupting Capacity Rating	65
Amperage	200 A
Device Type	Convertible
Enclosure	Indoor Type 1 Enclosure, Combination
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	0
1" Space	20
1/2" Space	42, 4, 24, 16, 20, 32, 40
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Indoor Load Center 1 page outline drawing in pdf format.	10103091-SH19	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.