



Representative Image

**Catalog No. TM4020CCU**

**Description: 200A 40CT 1P3W 120/240V 22K IC COMB**

**UPC No 783164112627**

**Products > Load Centers > Residential Load Centers > Single Phase - USA**

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit [www.geelectrical.com](http://www.geelectrical.com)

**Descriptors**

Category	Single Phase - USA
GO Schedule	RD

**Specifications**

Input/Output Voltage	120/240V ac
Type	Standard
Interrupting Capacity Rating	22
Amperage	200 A
Device Type	Main Breaker
Enclosure	Indoor Type 1 Enclosure, Combination
UL/CUL Listing	UL
Phase	1 Phase
1" Space	40
1/2" Space	0
Feed	Either
Door	Yes
GSA Compliance	Yes

## Publications

Title	Publication No.	Publication Type
<a href="#">Indoor Load Center</a> 1 page outline drawing in pdf format.	10103091-SH23	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.