



Representative Image

Catalog No. TLM3220CCU

Description: FLD CNVRTB 200A 32CRK 22K IC COMB

UPC No 783164112764

Products > Load Centers > Residential Load Centers > Single Phase - USA

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit www.geelectrical.com

Descriptors

Category	Single Phase - USA
GO Schedule	RD

Specifications

Input/Output Voltage	120/240V ac
Type	Standard
Interrupting Capacity Rating	65
Amperage	200 A
Device Type	Convertible
Enclosure	Indoor Type 1 Enclosure, Combination
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	0
1" Space	32
1/2" Space	40, 42, 4, 24, 16, 20, 32
Feed	Either
Door	Yes
GSA Compliance	No

Publications

Title	Publication No.	Publication Type
Indoor Load Center 1 page outline drawing in pdf format.	10103091-SH21	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.