




## SL12025TL - 2" ICAT Line Voltage Downlight



### Product Specifications:

Lamp - One 120V max. 25W Aluminum backed MR16 or appropriate LED (not included)

Recommended LED - TCP Elite GU10 Dimmable 7W

Socket - GU10

Thermal Protection - Thermally protected for over-lamping



Dimming - Can be used with all standard TRIAC dimmers. LED dimming dependent on lamp.

Junction Box - Constructed of fire-rated plastic. Maximum 2 No. 12 AWG 90°C cables (1 in, 1 out). Armoured Cable adaptor included. 5 wire cable connection terminal. Approved for feed-through wiring. Double insulated fixture, no grounding required.

Housing - IC rated. Air Tight as per ASTM E283 Standard. Adjustable butterfly clips for ceiling material thicknesses of  $\frac{1}{4}$ " to  $1\frac{1}{4}$ ". Powder coated steel construction. Approved for use in damp locations / wet locations (with WLTL accessory).

Trim - Round. Non-directional. Finishes available: White (WH), Chrome (CH), Brushed Steel (BS), Bronze (BZ), Black (BL). Powder Coated. Lamp secured with Twist & Lock mechanism.

Cut Out Hole Diameter -  $2\frac{3}{4}$ " (70mm)



Project:

Product Code: (Please circle desired finish)

SL12025TL - WH CH BS BZ BL

Twice Bright Lighting Co. Ltd.

108 - 11860 Hammersmith Way · Richmond, BC · Canada · V7A 5G1  
(778) 297-2121 · (888) 484-7295 · info@twicebright.com · www.twicebright.com