

Straight Blade Devices
15A, 125V, 2 Pole, 3 Wire Grounding
USB Charger Receptacles

HUBBELL



Features

- Two USB ports 3.8 Amp, 5V DC, type A, class 2.0
- Tamper-Resistant decorator duplex receptacle
- Green LED indicator to show USB power available
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

Ordering Information

Description	Device Color	UPC	Catalog Number
USB 15 A, 125V AC Charger Tamper-Resistant receptacle,Two USB Type 2.0 ports 3.8 Amp, 5 Volt DC	Ivory	883778304583	USB15X2I

Listings

cULus listed to UL498

Specifications


Face	RTP
Base	RTP
LED	Green Indicator
Contacts	Plated steel
Clamp	Plated steel
Terminal Screws	Plated steel
Mounting Strap	.040" Zinc plated steel
Mounting Screws	Zinc plated steel
USB Port	Stainless Steel

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Port	Stainless steel Rated for 10,000 plug insertions and removal
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)



15A 125V
NEMA 5-15R
UL CSA
0.5 HP



Complementary Products

Wallplate or Weatherproof Cover StyleLine® Decorator Opening

Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

