



8269-12: One Light Outdoor Post Lantern



Collection: Sebring

Outdoor Post Lantern Top with Black Finish and Clear Seeded Glass.

Eye-catching style, in a black finish over aluminum. Clear seeded glass adds just the right sparkle. Fits 3" post (sold separately).

UPC #:785652826924

Finish: Black (12)

Dimensions:

Diameter:	11 1/4"	Extends:	16"
Height:	15 3/4"	Wire:	6 1/2"
Weight:	3.4 lbs.	Bulb Appearance:	Clear

Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

- 1 Body - Aluminum - Black
- 1 Bracket - Aluminum - Black
- 1 Holder - Aluminum - Black

Safety Listing:

- Safety Listed for Wet Locations
- Safety Listed for Wet Locations

Instruction Sheets:

- English (HC-534)
- French (F-013)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Clear Seeded	1					5				

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8269-12	1	785652826924	18	14	17	2.479	6.1	250	Yes
NJ Pallet		24		48	40	72	80	146.4		No
NV Pallet		24		48	40	72	80	146.4		No