



FM273ORB: 3 - Light Indoor Flush Mount

Dimensions:

Diameter: 16 1/2" **Wire:** 8"
Height: 5 3/4"
Weight: 13.5 lbs.

Bulbs:

3 - Medium A19 60w Max. 120v - Not included

Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
-

Material List:

1 Body - Steel - Oil Rubbed Bronze

Safety Listing:

Safety Listed for Dry Locations
 Safety Listed for Dry Locations

Instruction Sheets:

English (FM273)



Collection: Barrington

UPC #: 014817330854

Finish: Oil Rubbed Bronze (ORB)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Etched Glass	Opal Etched	1				4	14 1/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Mounting Plate	1	4				

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
Individual	FM273ORB	1	014817330854	18.75	18.75	9.25	1.882	13.71	125	Yes

Feiss reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Feiss . In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Feiss 1/2 A Generation Brands Company.

NJ Pallet		34		48	40	71	78.889	466.14		No
NV Pallet		34		48	40	71	78.889	446.14		No