



Communication Technologies

[United States](#) > [Electronics](#) > [Communication Technologies](#) > [Communication Technologies Product Catalog](#) > [Copper Connectors and Splices](#) > 3M™ Scotchlok™ IDC Butt Connector UR Box

3M™ Scotchlok™ IDC Butt Connector UR Box

3M ID 80611327885 UPC# 00051115262302 Part Number UR(BX)

[Print](#)

3M™ Scotchlok™ IDC Butt Connector UR is filled with a sealant which offers immense resistance to moisture. It withstands a temperature range of -40 to 140 degrees F (-40 to 60 degrees C).

3M™ Scotchlok™ IDC Butt Connector UR is designed to accommodate 2 or 3 conductors. This connector is ideal for butt splicing operations. This connector is perfect for use on PIC cable where moisture resistance is required.

- Designed to accept 2 or 3 solid, copper conductors
- Moisture-resistant
- Suitable for butt splicing applications
- 0.06-in O.D. insulation
- Accommodates 26 to 19 AWG conductor sizes
- Durable polycarbonate construction
- Comes in red color
- Withstands a temperature range of -40 to 140 degrees F (-40 to 60 degrees C)
- 100/box, 10 boxes/case

Need Help?

Questions? We can help
[Contact Us](#)

Overview**Documents****Specifications**

Brand	Scotchlok
Cable Type	PIC
Composition	Filled
Connector Type	Butt/2 or 3 Conductor
Family	Scotchlok
Flame Retardant	No
Insulation Outside Diameter	0.06 Inch
Minimum Order	1000 each
Operating Temperature Range	-40 to 140 Degree Fahrenheit
Packaging	10 Boxes per Case
Product Type	Connector
RUS Listed	Yes/BA
Solution for	Access Network: FTTH/FTTB/CATV, Access Network: xDSL, Wireless Network: Backhaul
Trademark	Scotchlok
Wire Gauge	26 - 19 AWG

3M Communication Technologies: [Connect to MyTelecom](#) | [Where to Buy](#) | [Contact Us](#) | [View Mobile Site](#)

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.