



SF289BUS: 3 - Light Indoor Semi-Flush Mount



Dimensions:

Diameter:	16"	Wire:	8" (color/Black/White)
Height:	12 1/2"	Mounting Proc.:	Cross Bar
Weight:	12.72 lbs.	Connection:	Mounted To Box

Bulbs:

3 - Medium A19 60w Max. 120v - Not included

Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
-

Material List:

1 Body - Steel - Burnished Silver

Safety Listing:

Safety Listed for Dry Locations
Safety Listed for Dry Locations

Instruction Sheets:

English (SF289)
Trilingual (English, Spanish, and French) (SF289BUS)

Collection: Lucia

UPC #: 014817412345

Finish: Burnished Silver (BUS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Fabric	Beige	1				12 1/2	13 3/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	8					

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	SF289BUS	1	014817412345	19.75	19.5	16	3.566	20.3	150	Yes

Feiss reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Feiss . In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Feiss 1/2 A Generation Brands Company.

NJ Pallet		28		48	40	72	80	568.4		No
NV Pallet		28		48	40	77	85.556	544		No