



Powering Business Worldwide

pe.eaton.com

BR style 1-inch commercial loadcenter

3BR3042B200R

UPC: 786676440752

Dimensions: 3.88 IN * 14.31 IN * 34.13 IN (L * W * H)

Notes: Listed for use as service entrance equipment and shipped with a neutral bonding strap preattached, the maximum rating of the panel is the main breaker rating when used as service entrance equipment.

Warranty: 10 year

Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main circuit breaker
- **Amperage Rating:** 200A
- **Box Size:** L1r
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 42
- **Number Of Spaces:** 30
- **Number Of Wires:** Four-wire
- **Phase:** Three-phase
- **Wire Size:** #1-250 kcmil Cu/Al at 60°C or 75°C
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 208Y/120 or 240V

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type BR 3-Phase Loadcenters](#)
- [3-Phase Loadcenter Program](#)



Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.