

N7899-HGI



UPC Code: 07847760183

Country Of Origin: China

N7899-HGI

Item Description

20 Amp, 125 Volt Receptacle, Hospital Grade, 20 Amp Feed-Through, SmartLock Pro Slim GFCI, monochromatic, back and side wired, wallplate and self grounding clip included - Ivory

Technical Information

AC Horsepower Ratings

At Rated Voltage: 1 HP

Electrical Specifications

Voltage: 125 Volt

Amperage: 20 Amp

Feed-Through Current: 20 Amp

Frequency (Hertz): 60

Short Circuit Current Rating: 10kA

Wire: 3

Pole: 2

Environmental Specifications

Operating Temperature: -35C to +66C

Flammability: Rated V-0 per UL94

Material Specifications

Strap Material: Galvanized Steel

Face Material: PBT

Body Material: Polycarbonate

Terminal Screws: Plated Steel

Grounding Screw: Plated Steel

Clamps: Brass

Mechanical Specifications

Product ID: Ratings permanently marked on device

Terminal Accom.: 14-10 AWG

Performance Data

Diagnostics: LED

Trip Level: Class A, 5mA plus or minus 1mA

Product Features

Color: Ivory

Standards and Certifications

UL 498: File E13399

CSA C22.2 No. 42: File LR-57811

UL 943: File E48380

UL Fed Spec WC-596: Yes

ANSI: C-73

NOM: 057

NEMA: WD-1 & WD-6

Warranty

Warranty: 2 Year Limited

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
JOB NUMBER:		

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

