

SF285BRB/OBZ: 3 - Light Indoor Semi-Flush Mount

Dimensions:

Diameter: 21 1/4" **Wire:** 8" (color/Black/White)
Height: 17 3/8" **Connection:** Mounted To Box
Weight: 14.74 lbs.

Bulbs:

3 - Medium A19 60w Max. 120v - Not included

Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
-

Material List:

1 Body - Steel - British Bronze / Oxidized Bronze
 1 Canopy - Steel - British Bronze / Oxidized Bronze

Safety Listing:

Safety Listed for Damp Locations / IC
 Safety Listed for Damp Locations / IC

Instruction Sheets:

English (SF285)



Collection: Marcella

UPC #: 014817408812

Finish: British Bronze / Oxidized Bronze (BRB/OBZ)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Hardback w/ Fabric	Beige	1				6 3/4	17 1/2				
Diffuser	Glass	Undefined	1					17				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy				7 1/8		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
--------------	-----------	----------	-----	--------	-------	--------	------	--------	------------	----------

Individual	SF285BRB/OBZ	1	014817408812	24	17.38	24	5.793	20.75	250	Yes
NJ Pallet		12		48	40	77	85.556	249		No
NV Pallet		12		48	40	77	85.556	249		No