



GE  
Lighting

11367 - GE S6 - Appliance

6S6 TRAY

Product Photo



#### GENERAL CHARACTERISTICS

Base Description	Candelabra Screw
Base Type	Screw-In
Bulb Finishes and Colors	Clear
Filament	C-7A
Rated Life Hours-nominal	1500 h
Primary Application	Appliance
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E12
Bulb Shape	S6

#### PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	7
Initial Lumens-nominal	41 lm

#### PRODUCT INFORMATION

Product Code	11367
Description	6S6 TRAY
Alternative Unit Of Measure	EACH
Standard Package Quantity	240
Ean UPC	043168113670
Standard Package GTIN	00043168113670
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	240
Sales Unit	Each
UCC	043168113670
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168113670
Standard Package GTIN	10043168113677
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168113670

#### DIMENSIONS

Diameter	0.75 in
----------	---------

#### ELECTRICAL CHARACTERISTICS

Wattage	6 W
Input Voltage [nom]	120 V

