



SPECIFICATION SHEET

B11 Torpedo Incandescent Lamp

Item Number **03293**

Specifications

Energy Used (Watts).....	60
Domestic Code	60B11/VR
Volts	120
Brightness (Lumens)	570
Average Rated Hours	1500
Life (in years)*	1.3
Dimmable	Yes
Filament Type.....	C7A
Estimated Yearly Energy Cost**	\$7.23
Package Type.....	Box
Country of Origin.....	China



Physical Characteristics

Finish.....	Clear
Base.....	Medium (E26)
MOL	3.63"

Vibration Resistant lamps are designed for vibration service only.

*Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

© WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.

Used under license by Westinghouse Lighting. All Rights Reserved.