



BURNDY Catalog Number	YA25TC38
UPC Number	781810019672
Description	CU HYLUG - 1/0 STR - 3/8
Status	Active

Web Use
BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Strip Length	1-7/16
Length (in)	2.61
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Long
Thickness	0.12
B Length (in)	1.38
Pad Width (in)	0.75
General	
Number of Holes	1
Product Description	Copper Compression lug, 1 Hole w/o Inspection Window, 1/0 AWG, 3/8" Stud, Long Barrel, Tin Plated
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	1/0
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Pink
Plated (Yes or No)	Y
Index Number	12
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies
47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175

