



On Line Catalog



BURNDY Catalog Number YA282TC38
UPC Number 7818108212511
Description CU HYDENT-4/0AWG-(2) 3/8
Status Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	3.99
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Long
Thickness	0.14
B Length (in)	1.62
Pad Width (in)	1.02
E - in	1.00
Strip Length	1-11/16

General

Number of Holes	2
Product Description	Copper Compression lug, 2 Hole w/o Inspection Window, 4/0 AWG, 3/8" Stud, 1" Stud hole spacing, Long Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	4/0 AWG
DLO Size (Range)	N/A
Copper Stranded (Range)	4/0 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Purple
Plated (Yes or No)	Y
Index Number	15
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us