



On Line Catalog



BURNDY Catalog Number

YA282NTC38

UPC Number

7818100198944

Description

CUHYDENT 4/0AWG (2) 3/8

Status

Active

Web Use

BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	4.74
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Long
Thickness	0.14
B Length (in)	1.62
Pad Width (in)	1.02
E - in	1.75
Strip Length	1-11/16

General

Number of Holes	2
Product Description	Cu Comp Terminal Code Cond, Bvl Entry, 2 Hole/W/O/InspWindow, 4/0 AWG Code, 200 Navy , 600 V-35 kV, 3/8" Stud, 1.75" Spacing, Lng bbl, Purple, 15 Index

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	4/0 AWG
DLO Size (Range)	N/A
Copper Stranded (Range)	4/0 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Purple
Plated (Yes or No)	Y
Index Number	15
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

BURNDY Technical Services

Hours: 8:00 AM - 5:00 PM
Monday - Friday