



Measurements:

<u>Height</u>	<u>Width</u>
16.00"	25.00"
<u>Max OAH</u>	
16.08"	
<u>Hanging Weight</u>	
11.68 lb	

Lamping:

Incandescent MB Incandescent	5,750 Rated Lumens
5.00 100W MB Incandescent	Color Temperature
500 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
14.68 lb	10.50"	12.50"	22.50"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209269927	Yes	

Finish:

Satin Nickel SN

Glass:

Marble MR

Material:

Steel

Certification:

Dry Location
Location

Additional:

MB Incandescent (Not Included)