



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

BIBS6003
 7818102241066
 600-4 ONE SIDED UNITAP,4 IN L
 Active

Web Use
 BURNDY Product Line

Width (in)
 Hex Size (Key)
 Length (in)
 Height (in)

Dimensional
 2.38
 3/8
 4.00
 2.75

Min Voltage Rating

Electrical
 600

Number of Ports
 Number of Screws

General
 3
 3

Product Description

Aluminum Multiple Tap
 Connector, Clear Insulated, 3 Port,
 1 Sided Entry, 4 AWG-600 kcmil,
 Al/Cu Rated

Aluminum Size (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)
 4 AWG-600 kcmil
 N/A
 4 AWG-600 kcmil

Type of Hardware
 Type of Plating
 Insulation Type
 Plated (Yes or No)
 Product Material

Physical
 Aluminum
 Unplated
 Plastisol
 N
 Aluminum

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications
 N
 Y
 Y
 Compliant
 N
 N
 UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175