



## Specification Sheet

# Commercial Service<sup>®</sup> Appliance

# A15 General Purpose Incandescent Lamp, 2-Pack

Order Number **04503**

## Specifications

Energy Used (Watts).....	15
Domestic Code.....	15A15/F/130 2PK
Volts.....	130
Brightness (Lumens) .....	90
Average Rated Hours .....	2500
Life (in years)* .....	2.3
Dimmable.....	Yes
Filament Type .....	C9
Light Center Length (LCL) .....	2 5/8"
Estimated Yearly Energy Cost** .....	\$1.81
Country of Origin.....	China



## Physical Characteristics

Finish.....	Frost
Base.....	Medium
MOL.....	3 3/8"

\* Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee  
™“Westinghouse” and “You can be sure...if it’s Westinghouse” are all registered trademarks of Westinghouse Electric Corporation.

