



BURNDY Catalog Number YA8C2TC14  
 UPC Number 781810019696  
 Description CUHYLUG 8 STR 2 HOLE 1/4  
 Status Active

Web Use  
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.33
Tongue Type	Standard
Barrell Style	Chamfered
Barrel Type	Long
Thickness	0.08
B Length (in)	0.81
Pad Width (in)	0.44
E - in	0.62
Strip Length	7/8
General	
Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/o Inspection Window, 8 AWG/6 AWG, 1/4" Stud, 5/8" Stud Hole Spacing, Long Barrel, Tin Plated
Conductor(s)	
Copper Solid Size (Range)	8 AWG
Copper Stranded (Range)	8 AWG
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Red
Plated (Yes or No)	Y
Index Number	49
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA  
 47, industrial Park Drive  
 Manchester NH03109

BURNDY Technical Servcies  
 47, industrial Park Drive  
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
 Monday - Friday  
 Phone: 000-346-4175

