



Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)

[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Electrical Tape, Mastics & Special Use](#) > [Vinyl Electrical Tapes](#) > [Scotch® Premium Vinyl Electrical Tape Super 88, 3/4 in x 66 ft](#)

[Find An Account Rep](#)[Where To Buy \(Find A Distributor\)](#)[Contact Us](#)

Scotch® Premium Vinyl Electrical Tape Super 88, 3/4 in x 66 ft

3M ID 80610833867 UPC# 00054007061434 Part Number 88-SUPER-3/4X66FT

[Print](#)



Scotch® Vinyl Electrical Tape Super 88 is a premium grade, 8.5-mil thick, all-weather vinyl insulating tape. It is designed to perform continuously between a temperature range of 0–220°F (-18–105°C). It has an excellent resistance to UV rays, abrasion, moisture, alkalies, acids, corrosion and varying weather conditions.

- 3/4 in x 66 ft, Black
- Premium grade, 8.5-mil thick, all-weather vinyl insulating tape
- Temperature range of 0–220°F (-18–105°C).
- Excellent resistance to UV rays, abrasion, moisture, alkalies, acids, corrosion and varying weather conditions
- Provides primary electrical insulation for splices up to 600V
- UL Listed and CSA Certified

Need Help?

Questions? We can help
[Contact Us](#)



Overview

Documents

For professional use, this tape combines the flexibility of a PVC backing with excellent electrical insulating properties to provide primary electrical insulation for splices up to 600V and protective jacketing. UL Listed and CSA Certified.

Specifications

Adhesion_to_Steel	2,7 N/cm
Adhesive_Material	Rubber Resin
Adhesive_Type	Rubber
Agency_Approvals	CSA Certified, UL Listed
Backing_Material	Vinyl
Backing_Thickness_metric	22 mm
Brand	Scotch
Breaking_Strength	35 N/cm
Chemical_Resistant	Yes
Color	Black
Dielectric_Strength	1150 V/mil
Elongation_at_Break	250%
Family	Scotch® Vinyl Electrical Tape Super 88
Flame_Retardant	Yes
Length	66 Linear Foot
Length_metric	20 m
Material	PVC
Operating_Temperature_Celsius	Up to 105 Degree Celsius
Operating_Temperature_Range_Celsius	-18 to 105 Degree Celsius
Operating_Temperature_Range_Fahrenheit	0 to 220 Degree Fahrenheit
Product_Family	Scotch® Vinyl Electrical Tape Super 88
Product_Type	Vinyl Tape, Vinyl Electrical Tapes

RoHS_2011_65_EU_Compliant	Yes
RoHS_EU_Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Rolls_per_Carton	10
Rolls_per_Case	100
Self_Sticking_Amalgamating	No
Self-Extinguishing	Yes
Shelf_Life	5 Year
Specifications	VDE 0340 TEIL 3-1, SS 404 09 75, Mil-I- 24391C, ASTM D-3005 type 2
Suitable_for_High_Voltage	No
Tape_Grade	Premium
Tape_Type	Vinyl
Thickness	8.5 mil
Thickness_metric	0.22 mm
Trademark	Scotch
UL_File_Number	E129200
UV_Resistant	Yes
Voltage_Application	Low Voltage
Voltage_Rating	600 V
Vulcanizing	No
Width	0.75 Inch
Width_metric	19 mm

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.