



GE  
Lighting

12658 - GE A15

15A15

Product Photo



### GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Bulb Finishes and Colors	Inside frost
Filament	C-9
Rated Life Hours-nominal	2500 h
Primary Application	Ceiling Fan
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E26
Bulb Shape	A15

### PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	8
Initial Lumens-nominal	115 lm

### PRODUCT INFORMATION

Product Code	12658
Description	15A15
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168909839
Standard Package GTIN	00043168126588
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168126588
Alternative Unit Of Measure	EACH
Standard Package Quantity	120
Ean UPC	043168909839
Standard Package GTIN	00043168909839
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	120
Sales Unit	Each
UCC	043168126588

### DIMENSIONS

Diameter	1.87 in
----------	---------

### ELECTRICAL CHARACTERISTICS

Wattage	15 W
Input Voltage [nom]	130 V

