



98606SW-12: 12V 1' LED Tape Strip 3000K



Dimensions:

Length:	12"	Volts:	12
Width:	3/8"	Watts:	3
Height:	1/8"	Watts Consumed:	3
		Watts Rated:	3
		Hours Rated:	50000
		Lumens:	150
		Bulb Temp:	3000 °K
		CRI:	85

Features:

- This advanced LED technology is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

Material List:

Safety Listing:

cETL Listed for Damp Locations

Instruction Sheets:

English (HC-1894FS)

Collections: 12V LED Tape Strips (Primary)
Ambiance LED Under Cabinet

Ambiance LED Tape provides ultra-low profile LED linear lighting that can be mounted securely in numerous applications with its high-endurance 3M™ adhesive backing. Ambiance LED Tape is dimmable on magnetic and electronic low voltage systems. For magnetic systems, a standard incandescent or magnetic low voltage (MLV) dimmer can be used. For electronic, an electronic low voltage (ELV) dimmer is recommended.

Versatile LED linear lighting, ultra low profile 1/8" H x 3/8" W - easily fits into any space. Flexible - bend lengthwise or curve laterally.

Available in a variety of lengths including 1ft, 5ft, 16ft and 2 inch sections and with wide variety of connectors. Field cuttable at every 2 inches to end a run

Provide and feel of halogen and xenon with energy savings of up to 90%

3000K LED Tape produces 150 lumens per foot and consumes 3 watts per foot.

Lumen package is comparable to traditional undercabinet lighting 10W xenon to 20W halogen 4 inch to 6 inch on center

Long 40,000 hour life last 20X's longer than halogen for maintenance free operation

Color accurate illumination CRI 85, 3000K color- improves visibility and perceived brightness

12VAC operation, dimmable with a wide range of incandescent and ELV dimmers, can be connected to 12VAC Ambiance Lx systems

CETL listed, damp location

Environmentally friendly contains no mercury and emits no UV or IR

UPC #:785652158742

Finish: Black (12)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	98606SW-12	1	785652158742	13.78	1.5	0.75	0.009	0.1	85	Yes
Master Pack	98606SW-12	10	10785652158749	14.25	4	1.75	0.058	0.8	85	Yes
Shipping Master	98606SW-12	200	20785652158746							