

PRODUCT OVERVIEW

PowerMark Plus Load Centers are designed and built for faster installation and more dependable performance. UL Listed. Three-phase, Three-wire, 120/240 Volts ac. Factory Installed Main Lug. All neutral holes are rated for 14-4 wire. 100% rated split neutral on each side.

- Commercial load center
- Three phase
- Four wire
- 208Y/120 Volts AC
- Top Feed
- Factory Installed Main Lug
- Outdoor
- MFG Model # : TL12412R
- MFG Part # : TL12412R

[Return To Top](#)

SPECIFICATIONS

Assembled Depth (in.)	4.6 in	Assembled Height (in.)	21.2 in
Assembled Width (in.)	12.5 in	Color/Finish	Gray
Electrical Product Type	Load Center	Energy Star Compliant	No
Height	21.2 in	Load Center Type	Main Lug
Load center depth (in.)	22.063	Load center height (in.)	5.375
Load center width (in.)	13.563	Manufacturer Warranty	Lifetime Warranty
Maximum Amperage (amps)	125 A	Mounting type	Plug In
Number of Spaces	12	Number of phases	3
Product Series	GE	Product Weight (lb.)	20.929
Returnable	90-Day	Voltage (volts)	120 V
Width	12.5 in		
