



## 5328-782: Two Light Ceiling Flush Mount



**Collection:** Webster

Two Light Wall or Ceiling Fixture in Heirloom Bronze Finish with White Bowl-Shaped Glass.

Two-light close to ceiling fixture with heirloom bronze finish and white glass.

**UPC #:**785652532870

**Finish:** Heirloom Bronze (782)

### Dimensions:

**Diameter:** 9 1/2"

**Height:** 5 3/4"

**Extends:** 5 3/4"

**Wire:** 6 1/2"

**Mounting Proc.:** Center Lock-Up

**Connection:** Mounted To Box

### Bulbs:

2 - Medium A19 60w Max. 120v - Not included  
2 - LED Medium A19 8w Max. 120v - Not included  
2 - LED Medium A19 13.5w Max. 120v - Not included

### Features:

- Fixture may be mounted on wall or ceiling.
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

### Material List:

1 Body - Steel - Heirloom Bronze

### Safety Listing:

Safety Listed for Damp Locations  
Safety Listed for Damp Locations

### Instruction Sheets:

English (HC-167)  
French (F-014)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Smooth White	1				4	9 1/2				

### Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	5328-782	1	785652532870	10.5	10.5	6.75	0.431	2.8	125	Yes
Master Pack		6	10785652532877	21.5	20.5	10.75	2.742	18.3	125	Yes
NJ Pallet		144		48	40	69.5	77.222	439.2		No
NV Pallet		144		48	40	80	88.889	508.2		No