

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3855-09

Melon

Two-light semi-flush with modern trumpet glass shades in a soft etched finish. This collection delivers a minimalist urban style and is finished in Brushed Nickel.

Category: Close-to-Ceiling

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Etched glass cone shaped bowl



Diameter: 13-5/16"

Height: 9-5/8"

Glass: 13-5/16" dia.

Height: 5-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling semi-flush mounted Mounting strap for outlet box included Canopy covers a standard 4" hexagonal recessed outlet box	Pre-wired 6" of wire supplied 120V	Quantity: 2 100W Medium Base Medium ceramic sockets	cCSAus Damp location listed 1 year warranty Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available