

Electrical Commercial and Industrial

Products | Documentation & Literature | News & Tradeshows | Support

United States > Energy > Electrical Commercial and Industrial > Products > Electrical Commercial & Industrial Products Catalog > Electrical Tape, Mastics & Special Use > Vinyl Electrical Tapes > Scotch® Vinyl Color Coding Electrical Tape 35, 3/4 in x 66 ft, Orange

Find An Account Rep

Where To Buy (Find A Distributor)

Contact Us

Scotch® Vinyl Color Coding Electrical Tape 35, 3/4 in x 66 ft, Orange

3M ID 80610834022 UPC# 00054007108696 Part Number 35-ORANGE-3/4



Scotch® Vinyl Electrical Tape 35 is a 7-mil thick polyvinyl chloride (PVC) color-coding tape. It operates over a wide range of temperatures – between 32–220°F (0–105°C). Outstanding electrical and mechanical properties make this tape excellent for use in phase identification, color coding of motor leads and piping systems, and for marking safety areas.

- 3/4 in x 66 ft, Orange
- 7-mil thick polyvinyl chloride (PVC) color-coding tape
- Temperature range of 32–220°F (0–105°C)
- Excellent for use in phase identification, color coding of motor leads and piping systems, and for marking safety areas
- Abrasion- and weather-resistant
- Flame-retardant; resists UV rays, abrasion, moisture, alkalies, solvents, many acids
- Stretches to conform to virtually any shape
- UL Listed and CSA Certified

• Print

Need Help?

Questions? We can help
[Contact Us](#)

Overview

Documents

Scotch® Vinyl Electrical Tape 35 is abrasion- and weather-resistant, with excellent mechanical and electrical insulation properties. It is also flame-retardant; resists UV rays, abrasion, moisture, alkalies, solvents, many acids. For indoor and weather-protected outdoor applications. Stretches to conform to virtually any shape that requires color-coded insulation. UL Listed and CSA Certified.

Specifications

Adhesive_Material	Rubber Resin
Agency_Approvals	CSA Certified, UL Listed
Backing_Material	Polyvinyl Chloride
Brand	Scotch
Breaking_Strength	17 lb/in
Color	Orange
Dielectric_Strength	1250 V/mil
Family	Scotch® Vinyl Color Coding Electrical Tape 35
Length	66 Linear Foot
Length_metric	20.1 m
Material	PVC
Operating_Temperature_Range_Celsius	0 to 105 Degree Celsius
Operating_Temperature_Range_Fahrenheit	32 to 220 Degree Fahrenheit
Product_Family	Scotch® Vinyl Color Coding Electrical Tape 35
Product_Type	Vinyl Tape, Vinyl Electrical Tapes, Electrical Insulating Tapes for Equipment Manufacturing
RoHS_2011_65_EU_Compliant	Yes
RoHS_EU_Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Rolls_per_Carton	10
Rolls_per_Case	100
Self_Sticking_Amalgamating	No

Self-Extinguishing	No
Specifications	VDE 0340-TEIL1
Suitable_for_High_Voltage	Yes
Tape_Grade	Premium
Tape_Type	Vinyl
Thickness	7 mil
Thickness_metric	0.177 mm
Trademark	Scotch
UV_Resistant	Yes
Voltage_Application	Low Voltage
Vulcanizing	No
Width	0.75 Inch
Width_metric	19 mm

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)
[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.